

自主离子平衡系统 Model 360A 静电消除风扇



特色

- CoreStat 自动离子平衡技术
- SSDC 离子产生设计
- 低离子平衡
- 异常讯号输出端子(FMS)
- 异常侦测 (高压源异常及离子平衡偏移)
- 小型尺寸适合安装于设备内或工作桌

优点

- 无须定期调整
- 4-20mA封闭回路和输出侦测器
- 明显异常显示灯号
- 声响报警
- 风扇后盖打开时自动停机
- 容易更换针尖及清洁
- 可与其他设备相容

特色

CoreStat 自主型离子平衡技术，型号360A可应用于在许多制程内，例如封测产业，电子组装业等。本机器拥有自主控制在极佳的离子平衡不需额外要定期去做调整。

异常监视输出 (FMS) 可实时提供机器使用状态，并搭配LED灯号及警报声来提醒离子平衡偏移或高压异常等状态

Model 360A 静电消除风扇

规格

输入电压	24V DC, 4 Watt (Maximum)
离子产生模式	Steady-State DC Technology
离子平衡	< $\pm 20V$
除电效能	$\pm 1000V$ to $\pm 100V$ less than 5 sec at 30cm $\pm 1000V$ to $\pm 100V$ less than 8 sec at 60cm
风量	27 CFM
针尖材质	Tungsten 99.99%
异常设定	Visual (LED), Audio (Buzzer) when HV Power Fail
异常输出显示	FMS Interface
材质	Enclosure - ABS (Gray), Filter Cover - ABS (Black) Bracket-Aluminum Powder Coating
操作环境	Temperature: 15 - 35°C Relative Humidity: 35 - 75% RH
尺寸	80W x 110H x 64D mm without bracket 105W x 120H x 64D mm with bracket
重量	335g (with bracket)
保固	1 year


设备检测系统接口




Pin No.	Description
FMS 1	Alarm relay output
FMS 2	Relay common
FMS 3	Normal relay output
FMS 4	Current output for each operation
FMS 5	Current output reference ground

Facility Monitoring System Output Signals			
Condition	FMS 1~2	FMS 2~3	FMS 4~5
Normal state	Open	Closed	4~5mA
Alarm State	Closed	Open	17~20mA
No Power	Closed	Open	0mA

Sizes & Dimensions(mm)



Model 360A Discharge Time



深圳汉华半导体科技有限公司
Shenzhen Hanhua Semiconductor Technology Co., Limited

地址：深圳市宝安区松岗街道潭头社区恒生工业园第四栋
电话：0755-8524 0596 传真：0755-2300 1062
邮箱：chenyp@hanhwachina.cn
网站：www.hanhwachina.cn

